









Hammer Unions

Hammer Unions are widely usedly throughout the pipe connection of energy industry.

Whole structure is easy to disassembly, install, and convenient maintenance.

Luxe offers a full line of Hammer Unions available in butt weld, threaded, blind or sour gas.

Each union is throughly inspected to ensure long, dependable service in the most extreme conditions.

- 1. Steel material meeting ASTM and / or AISI standards.
- 2. Range from 1"to 8"with cold working pressures frome 500to 15,000 PSI.
- $3. Color \ coded \ for \ quick \ identification.$
- 4. Fully interchangedable with most major brands of Hammer Unions.
- 5. Rigorous inspection checks throughout Manufacturing.
- 6.BSP or NPT thread unions can be supplied upon request.





















Luxe Hammer unions/Clamp hub availability referebce chart

Connection

Fig.100

Conne	ction	Pressure Ra	ting				Size					
Female	male	Cold working	Test	1"	1-1/2"	2"	2-1/2"	3"	4"	5"	6"	8"
SUB×NPT	SUB×NP	T 1,000	1,500			√	√	√	√	√	√	√
BW SUB	Blind	1,000	1,500			√		√	√	√	√	
SUB×NPT	Blind	1,000	1,500			√		√	√	√	√	
SUB×NPT	Dust Cap	1,000	1,500					√	√	√		

Fig	.200
•	

			1"	1-1/2"	2"			4"	5"	6"	8"
SUB×NP	T 2,000	3,000	√	√	√	√	√	√	√	√	√
BW SUB	2,000	3,000							√		
BW SUB	2,000	3,000			√		√	√	√	√	
Dust Cap	2,000	3,000			√						
	SUB×NP BW SUB BW SUB	male Cold working SUB×NPT 2,000 BW SUB 2,000 BW SUB 2,000	male Cold working Test SUB×NPT 2,000 3,000 BW SUB 2,000 3,000 BW SUB 2,000 3,000	male Cold working Test 1" SUB×NPT 2,000 3,000 √ BW SUB 2,000 3,000 BW SUB 2,000 3,000	male Cold working Test 1" 1-1/2" SUB×NPT 2,000 3,000 √ √ BW SUB 2,000 3,000 ✓ BW SUB 2,000 3,000	male Cold working Test 1" 1-1/2" 2" SUB×NPT 2,000 3,000 √ √ √ BW SUB 2,000 3,000 ✓ BW SUB 2,000 3,000 ✓	male Cold working Test 1" 1-1/2" 2" 2-1/2" SUB×NPT 2,000 3,000 ✓ ✓ ✓ ✓ BW SUB 2,000 3,000 ✓ ✓	male Cold working Test 1" 1-1/2" 2" 2-1/2" 3" SUB×NPT 2,000 3,000 √ √ √ √ √ BW SUB 2,000 3,000 √ √ √ √	male Cold working Test 1" 1-1/2" 2" 2-1/2" 3" 4" SUB×NPT 2,000 3,000 √<	male Cold working Test 1" 1-1/2" 2" 2-1/2" 3" 4" 5" SUB×NPT 2,000 3,000 √	male Cold working Test 1" 1-1/2" 2" 2-1/2" 3" 4" 5" 6" SUB×NPT 2,000 3,000 √



remaie	male Co	ia working	lest	1	1-1/2	2	2-1/2	3	4	Э	О	ō
SUB×NPT	SUB×NPT	2,000	3,000	√	√	√	√	√	√	√	√	√
SUB×NPT	Blind	2,000	3,000		√							
Dust Cap	$SUB{ imes}NPT$	2,000	3,000		√				√			
BW SUB	BW SUB	2,000	3,000						√			
BW SUB	Blind	2,000	3,000						√			

Pressure Rating

Size

6

Conn	ection	Pressure Rating		Size								
Female	male	Cold working	Test	1"	1-1/2"	2"	2-1/2"	3"	4"	5"	6"	8"
BW SUB	Blanking u	nion 2,000	3,000						√			









Luxe Hammer unions/Clamp hub availability referebce chart

Connection Pressure Rating Size Female male Cold working Test 1" 1-1/2" 2" 2-1/2" 3" 4" 5" 6" 8"



SUB×NPT	$SUB \times NPT$	6,000	9,000	√	√	√	√ √
BW SUB	BW SUB	6,000	9,000	√	√		
BW SUB	Blind	6,000	9,000			√	√ √

Fig.1	002
Đ	AN

Conne	ction	Pressure Ra	ting				Size					
Female	male	Cold working	Test	1"	1-1/2"	2"	2-1/2"	3"	4"	5"	6"	8"
SUB×NPT	SUB×NP	Γ 10,000	1,500	√		√		√	√			
BW SUB	BW SUB	10,000	1,500	√		√		√	√			



Conne	ection	Pressure Ra	iting				Size					
Female	male	Cold working	Test	1"	1-1/2"	2"	2-1/2"	3"	4"	5"	6"	8"
SUB×NPT	SUB×NPT	Г 15,000	22,500	√	√	√		√				
BW SUB	BW SUB	15,000	22,500	√	√	√		√	√	√	√	



Fig.1502

Connec	ction	Pressure Rating	Size
Female	male	Cold working Test	1" 1-1/2" 2" 2-1/2" 3" 4" 5" 6" 8"









BODtech Sp. z o.o. ul. Mszańska, 1a 44-304 Wodzisław Śląski

bodtech@bodtech.pl tel. +48 503834570 skype: bodtech

